


# ULTRA LITE

Very easy-to-adapt and accept with the help of upgraded soft design.

**UltraLite** is a model of progressive developed to meet the needs of active wearers, for daily use.

Our Progressive UltraLite lens provides wide fields of vision, comfortable and light passages between areas and low level of peripheral disturbances.

**UltraLite** is very acceptable progressive due to immediate adaptation from the first experience and its soft design. It is an optimal solution for initial users, but also for experienced wearers who decide to change optical frames or model of progressives. It is designed to provide a constant optical quality for a long period, in sports activities, in use of digital devices, written media, in reading of small characters. Allows fast and dynamic focusing.



**DRP**  
**DISTANCE REFERENCE POINT**  
Reference point for far diopter measurement

**FC**  
**FITTING CROSS**  
Fitting cross position marks the pupil center position

**NRP**  
**NEAR REFERENCE POINT**  
Reference point for near diopter measurement



## ADVANTAGES

- ✓ Wide vision fields and low aberrations.
- ✓ Ideal solution for new progressive users.
- ✓ Very easy-to-adapt and accept with the help of upgraded soft design.

### COATING AVAILABLE

- UC** AuNaturel
- HC** GraniTe
- HMC** ClarityAR
- SHMC** ClarityPlus+
- BHMC** Blu-Coat
- UV** SunBlock
- TINT** TintIT
- MR** Reflective

### AVAILABLE LENS INDEX/MATERIALS

- |                |               |
|----------------|---------------|
| 1.50 CR-39     | 1.74 Hi-Index |
| 1.53 Trivex    | Transitions   |
| 1.56 Mid-Index | XTRActive     |
| 1.60 Hi-Index  | Drivewear     |
| 1.67 Hi-Index  | Revolution    |

### REMARKS

- ✓ Index 1.53 Trivex not tintable
- ✓ Index 1.74 not tintable
- ✓ Transitions available in Brown / Gray
- ✓ Transitions XTRActive available in Gray
- ✓ Polarized available in Brown / Gray / G-15
- ✓ Revolution available in Brown / Gray

### MHF'S

Minimum fitting height available in 16/18/20 mm

Our Progressive UltraLite design can be ordered with Individual parameters.

### FITTING NOTE

Align the fitting cross at the pupil center. For an appropriate choice of diameter and minimum mounting height, the suitable centering charts should be used.

### ULTRA LITE

The UltraLite progressive design fits in many different models and frame styles.

### SPECIAL REQUESTS

- ✓ Prism up to 5D
- ✓ Decentration
- ✓ PreCalc

### RANGE & AVAILABILITY

Please refer to page 34 for complete range and availability.